

## har-modular shell housing 20



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 02 09 500 2020                                                                |
| Specification      | har-modular shell housing 20                                                  |
| HARTING eCatalogue | <a href="https://harting.com/02095002020">https://harting.com/02095002020</a> |

### Identification

|                   |               |
|-------------------|---------------|
| Category          | Accessories   |
| Series            | har-modular®  |
| Type of accessory | Shell housing |

### Version

|               |                |
|---------------|----------------|
| Version       | Top/side entry |
| Strain relief | With cable tie |
| Locking type  | Locking lever  |
| 2 parts       | Yes            |
| Separable     | Yes            |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -55 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP20            |
| Isolation group                        | III             |

### Material properties

|                                           |                                                    |
|-------------------------------------------|----------------------------------------------------|
| Material (hood/housing)                   | Thermoplastic resin (PC)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | Black                                              |
| Material flammability class acc. to UL 94 | V-0                                                |
| Length                                    | 20.32 mm                                           |
| RoHS                                      | compliant                                          |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| ELV status                           | compliant     |
| China RoHS                           | e             |
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |
| Requirement set with Hazard Levels   | R26           |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 10                                         |
| Net weight                     | 282.99 g                                   |
| Country of origin              | Romania                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140427327                              |
| eCl@ss                         | 27440292 Connector component (accessories) |