

har-modular shell housing 70



Image is for illustration purposes only. Please refer to product description.

Part number	02 09 500 2070
Specification	har-modular shell housing 70
HARTING eCatalogue	https://harting.com/02095002070

Identification

Category	Accessories
Series	har-modular®
Type of accessory	Shell housing

Version

Version	Top/side entry
Strain relief	With cable tie
Locking type	Locking lever
2 parts	Yes
Separable	Yes

Technical characteristics

Limiting temperature	-55 ... +125 °C
Degree of protection acc. to IEC 60529	IP20
Isolation group	III

Material properties

Material (hood/housing)	Thermoplastic resin (PC) Fibre-glass reinforced
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
Length	71.12 mm
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	10
Net weight	424.36 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140427464
eCl@ss	27440292 Connector component (accessories)