

Acces. Uni Seal Yellow PG29 24-28mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5097
Specification	Acces. Uni Seal Yellow PG29 24-28mm
HARTING eCatalogue	https://harting.com/09000005097

Identification

Category	Accessories
Type of accessory	Cable gland

Technical characteristics

Tightening torque	≤20 Nm (depending on the cable and the seal insert used)
Wrench size	40
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 29
Clamping range	24 ... 28 mm

Material properties

Material (cable glands)	Metal
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead 2-(2'-Hydroxy-3'-tert-butyl-5'-methylphenyl)-5-chlorobenzotriazole (UV-326)
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	10
Net weight	106.8 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140001787
eCl@ss	27140801 Screwed cable gland (electrical)
ETIM	EC000441
UNSPSC 24.0	39121431