

DIN-Signal C/R shroud press-in a=7.50



Image is for illustration purposes only. Please refer to product description.

Part number	09 03 000 9955
Specification	DIN-Signal C/R shroud press-in a=7.50
HARTING eCatalogue	https://harting.com/09030009955

Identification

Category	Accessories
Series	DIN 41612
Type of accessory	Pin shroud
Description of the accessory	for female connectors type C for male connectors type R

Version

Termination length	16.2 mm
	17 mm
	20 mm
Fixing	Press-in fixing

Technical characteristics

Isolation group	IIIa ($175 \leq CTI < 400$)
PCB thickness	4.2 mm ± 0.5
	5 mm ± 0.5
	8 mm ± 0.5

Material properties

Material (accessories)	Thermoplastic
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Railway classification	F1/I2 acc. to NFF 16-101/102
------------------------	------------------------------

Commercial data

Packaging size	100
Net weight	5.2 g
Country of origin	Vietnam
European customs tariff number	85389099
GTIN	5713140004344
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400