



Pushing Performance
Since 1945

Han Q 8/0 ABDECKKAPPE



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 008 5407
Specification	Han Q 8/0 ABDECKKAPPE
HARTING eCatalogue	https://harting.com/09120085407

Identification

Category	Accessories
Series of hoods/housings	Han-Compact®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings

Version

Size	Han-Compact®
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

Material properties

Material (hood/housing)	Thermoplastic
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	7 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140017962
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467