

## Pneumatic contact male 4,0 mm



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 14 000 6153                                                                |
| Specification      | Pneumatic contact male 4,0 mm                                                 |
| HARTING eCatalogue | <a href="https://harting.com/09140006153">https://harting.com/09140006153</a> |

### Identification

|                            |                              |
|----------------------------|------------------------------|
| Category                   | Contacts                     |
| Type of contact            | Pneumatic contact            |
| Description of the contact | Without shut-off<br>Straight |

### Version

|                       |                 |
|-----------------------|-----------------|
| Gender                | Male            |
| Manufacturing process | Turned contacts |

### Technical characteristics

|                      |                |
|----------------------|----------------|
| Limiting temperature | -40 ... +80 °C |
| Operating pressure   | ≤8 bar         |
| Tube inner diameter  | 4 mm           |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (contacts)         | Delrin acetal |
| Material (seal)             | Buna-N        |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances  | Not contained |



**Pushing Performance**  
Since 1945

## Material properties

|                       |               |
|-----------------------|---------------|
| REACH SVHC substances | Not contained |
|-----------------------|---------------|

## Specifications and approvals

|          |                                                            |
|----------|------------------------------------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
|----------|------------------------------------------------------------|

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 10                                         |
| Net weight                     | 0.7 g                                      |
| Country of origin              | Germany                                    |
| European customs tariff number | 39269097                                   |
| GTIN                           | 5713140018280                              |
| eCl@ss                         | 27440204 Contact for industrial connectors |
| ETIM                           | EC000796                                   |
| UNSPSC 24.0                    | 39121522                                   |