

Adapter module w/o D-Sub, female -2cable




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 000 9933
Specification	Adapter module w/o D-Sub, female -2cable
HARTING eCatalogue	https://b2b.harting.com/09140009933

Identification

Category	Modules
Series	Han-Modular®
Type of module	Adapter module
Size of the module	Single module
Description of the module	for D-Sub 1 (9 poles)

Version

Gender	Female
Details	for two cables

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC) Zinc die-cast
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	25 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140018686
ETIM	EC000438
eCl@ss	27440218 Module for industrial connectors (data)