

## Han 1Mod-agg-M M4



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 14 001 0308                                                                |
| Specification      | Han 1Mod-agg-M M4                                                             |
| HARTING eCatalogue | <a href="https://harting.com/09140010308">https://harting.com/09140010308</a> |

### Identification

|                             |                          |
|-----------------------------|--------------------------|
| Category                    | Hoods / Housings         |
| Series of hoods/housings    | Han-Modular® Compact     |
| Type of hood/housing        | Bulkhead mounted housing |
| Description of hood/housing | Fixing hole for M4 screw |

### Version

|              |                                                                                                                                                                                                                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size         | Modular Compact                                                                                                                                                                                                                                                                                         |
| Locking type | Single locking lever                                                                                                                                                                                                                                                                                    |
| Details      | Rated voltage ≤630 V                                                                                                                                                                                                                                                                                    |
|              | Rated impulse voltage ≤6 kV                                                                                                                                                                                                                                                                             |
|              | Pollution degree 3                                                                                                                                                                                                                                                                                      |
|              | For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING. |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Mating cycles                          | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP65 locked condition                          |

### Material properties

|                         |               |
|-------------------------|---------------|
| Material (hood/housing) | Zinc die-cast |
| Surface (hood/housing)  | Nickel plated |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                 |
|--------------------------------------|-----------------|
| Material (seal)                      | NBR             |
| Material (locking)                   | Stainless steel |
| RoHS                                 | compliant       |
| ELV status                           | compliant       |
| China RoHS                           | e               |
| REACH Annex XVII substances          | Not contained   |
| REACH ANNEX XIV substances           | Not contained   |
| REACH SVHC substances                | Not contained   |
| California Proposition 65 substances | Yes             |
| California Proposition 65 substances | Lead<br>Nickel  |

## Specifications and approvals

|                |           |
|----------------|-----------|
| Specifications | IEC 61984 |
| Approvals      | CE        |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 80 g                                     |
| Country of origin              | Romania                                  |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140162839                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |
| ETIM                           | EC000437                                 |
| UNSPSC 24.0                    | 39121466                                 |