



Pushing Performance
Since 1945

Han 1Mod-agg-F M4



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0314
Specification	Han 1Mod-agg-F M4
HARTING eCatalogue	https://harting.com/09140010314

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Carrier hood
Description of hood/housing	Fixing hole for M4 screw

Version

Size	Modular Compact
Locking type	Single locking lever
Details	Rated voltage ≤630 V
	Rated impulse voltage ≤6 kV
	Pollution degree 3
	For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 locked condition

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated



Pushing Performance
Since 1945

Material properties

Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Specifications	IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	64.6 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140162846
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466