

Han GND cable to cable housing, 7,5-14mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 0730
Specification	Han GND cable to cable housing, 7,5-14mm
HARTING eCatalogue	https://harting.com/09140010730

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® GND
Type of hood/housing	Cable to cable housing

Version

Version	Top entry
Number of cable entries	1
Cable entry	1x Integrated
Locking type	Snap-in latches

Technical characteristics

Limiting temperature	-40 ... +85 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65
Cable diameter	7.5 ... 14 mm

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Green
Material (cable glands)	Polyamide (PA)
Colour (cable gland)	Yellow
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	2
Net weight	37 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019126
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466