

Han C PCB Module F



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 003 2710
Specification	Han C PCB Module F
HARTING eCatalogue	https://harting.com/09140032710

Identification

Category	Accessories
Type of accessory	PCB adapter
Description of the accessory	In the Han [®] C module

Version

Gender	Female
--------	--------

Technical characteristics

Rated current	40 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Limiting temperature	-40 ... +125 °C

Material properties

Material (insert)	Polycarbonate (PC)
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	564b7d75-7bf6-4cfb-acb1-2168eb61b675
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Commercial data

Packaging size	2
Net weight	31 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140190702
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415