

Han hinged frame plus, for 4 modules A-D




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 016 0361
Specification	Han hinged frame plus, for 4 modules A-D
HARTING eCatalogue	https://harting.com/09140160361

Identification

Category	Accessories
Series	Han-Modular®
Type of accessory	Hinged frame plus
Description of the accessory	for 4 modules A ... D

Version

Size	16 B
------	------

Technical characteristics

Conductor cross-section	1 ... 10 mm² PE (power side) 0.5 ... 2.5 mm² PE (signal side) The use of ferrules is recommended, conductor cross-section 10 mm² only with ferrule crimping tool 09 99 000 0374.
Stripping length	8 ... 10 mm
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material	Zinc die-cast Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	70 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140161962
eCl@ss	27440206 Module carrier frame for industrial connectors
ETIM	EC002312
UNSPSC 24.0	39121421