

## R 15-GG-AL



Image is for illustration purposes only. Please refer to product description.

Part number 09 15 000 0421

Specification R 15-GG-AL

HARTING eCatalogue <https://harting.com/09150000421>

### Identification

Category	Hoods / Housings
Series	R 15
Type of hood/housing	Hood

### Version

Number of cable entries	1
Cable entry	1x Pg 11
Locking type	Screw locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

## Material properties

California Proposition 65 substances	Lead Nickel
--------------------------------------	----------------

## Commercial data

Packaging size	10
Net weight	34.62 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021655
eCl@ss	27440224 Shell for circular connectors
ETIM	EC003556
UNSPSC 24.0	39121405