

SEK CAB FLAT STD AWG28/7 28P 100M



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 028 7004
Specification	SEK CAB FLAT STD AWG28/7 28P 100M
HARTING eCatalogue	https://harting.com/09180287004

Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

Version

Cable length	100 m
Number of cores	28
Core structure	AWG 28/7

Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Insulation resistance @ 20 °C	$\geq 20 \text{ M}\Omega \times \text{km}$

Material properties

Material (cable)	PVC
Colour (cable)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	CE
-----------	----

Commercial data

Packaging size	1
Net weight	5,400 g
Net weight	50 g/m
Country of origin	Great Britain
European customs tariff number	85444993
GTIN	5713140024977
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609