

## SEK CAB FLAT STD AWG28/7 50P 30,48m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 18 050 7001                                                                |
| Specification      | SEK CAB FLAT STD AWG28/7 50P<br>30,48m                                        |
| HARTING eCatalogue | <a href="https://harting.com/09180507001">https://harting.com/09180507001</a> |

### Identification

|               |                     |
|---------------|---------------------|
| Category      | System cabling      |
| Element       | Bulk cables         |
| Specification | Not assembled       |
| Type of cable | Copper cable (flat) |

### Version

|                 |          |
|-----------------|----------|
| Cable length    | 30.48 m  |
| Number of cores | 50       |
| Core structure  | AWG 28/7 |

### Technical characteristics

|                               |                                                  |
|-------------------------------|--------------------------------------------------|
| Limiting temperature          | -30 ... +105 °C unmoved<br>-20 ... +105 °C moved |
| Impedance                     | 100 $\Omega$                                     |
| Insulation resistance @ 20 °C | $\geq 20 \text{ M}\Omega \times \text{km}$       |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (cable)            | PVC           |
| Colour (cable)              | Grey          |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Specifications and approvals

|           |    |
|-----------|----|
| Approvals | CE |
|-----------|----|

## Commercial data

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Packaging size                 | 1                                              |
| Net weight                     | 2,925 g                                        |
| Net weight                     | 88 g/m                                         |
| Country of origin              | Germany                                        |
| European customs tariff number | 85444993                                       |
| GTIN                           | 5713140025240                                  |
| eCl@ss                         | 27061801 Data and communication cable (copper) |
| ETIM                           | EC003249                                       |
| UNSPSC 24.0                    | 26121609                                       |