

SEK CAB FLAT SH RND AWG28/7 64P 30,48m



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|-----------------------------------------------------------------------------|
| Part number | 09 18 064 7007 |
| Specification | SEK CAB FLAT SH RND AWG28/7 64P 30,48m |
| HARTING eCatalogue | https://hartin.com/09180647007 |

Identification

| | |
|---------------|----------------------|
| Category | System cabling |
| Element | Bulk cables |
| Specification | Not assembled |
| Type of cable | Copper cable (round) |

Version

| | |
|-----------------|----------|
| Cable length | 30.48 m |
| Number of cores | 64 |
| Core structure | AWG 28/7 |
| Shielding | Shielded |

Technical characteristics

| | |
|------------------------------|------------------------------------------------|
| Impedance | 100 Ω |
| Limiting temperature | -30 ... +75 °C unmoved -20 ... +75 °C moved |
| Conductor resistance @ 20 °C | ≤216 Ω/km |

Material properties

| | |
|------------------|-----------|
| Material (cable) | PVC |
| Colour (cable) | Grey |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |

Material properties

| | |
|--------------------------------------|---------------|
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|----------------|-------------------------|
| Specifications | UL 1581 UL PLCC, CL2 |
| Approvals | CE |

Commercial data

| | |
|--------------------------------|------------------------------------------------|
| Packaging size | 1 |
| Net weight | 7,000 g |
| Net weight | 220 g/m |
| Country of origin | USA |
| European customs tariff number | 85444993 |
| GTIN | 5713140025479 |
| eCl@ss | 27061801 Data and communication cable (copper) |
| ETIM | EC003249 |
| UNSPSC 24.0 | 26121609 |