

Han 3A-AK (Kunstst. sw)



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 003 5450
Specification	Han 3A-AK (Kunstst. sw)
HARTING eCatalogue	https://harting.com/09200035450

Identification

Category	Accessories
Series of hoods/housings	Han A®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	10
Net weight	6.03 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140039049
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467