

Han 4A-SC-F




Image is for illustration purposes only. Please refer to product description.

Part number	09 20 004 4711
Specification	Han 4A-SC-F
HARTING eCatalogue	https://harting.com/09200044711

Identification

Category	Inserts
Series	Han-Brid®
Identification	Han® 4 A SC
Description of the contact	for FO

Version

Gender	Female
Size	3 A
Number of contacts	4
Details	Please order contacts separately.

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance
Since 1945

Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Commercial data

Packaging size	2
Net weight	0.1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140039148
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors