

## Han 3A HMC-agw-QB



Image is for illustration purposes only. Please refer to product description.

Part number	09 20 203 0801
Specification	Han 3A HMC-agw-QB
HARTING eCatalogue	<a href="https://harting.com/09202030801">https://harting.com/09202030801</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> HMC
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled

### Version

Size	3 A
Locking type	Single locking lever
Field of application	Special hoods and housings for high mating cycles
Details	Han <sup>®</sup> 3 A HMC housings shall only be combined with housings from the Han <sup>®</sup> 3 A HMC portfolio.

### Technical characteristics

Tightening torque (fixing screw)	1 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Mating cycles	≥10,000
Note on the mating cycles	Mating cycles with other HMC components
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

### Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------



**Pushing Performance**  
Since 1945

## Material properties

Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	10
Net weight	74.3 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140170766
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466