



Pushing Performance  
Since 1945

# Han 16B IP67 housing-SL-C



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 30 016 1308                                                                |
| Specification      | Han 16B IP67 housing-SL-C                                                     |
| HARTING eCatalogue | <a href="https://harting.com/09300161308">https://harting.com/09300161308</a> |

## Identification

|                             |                           |
|-----------------------------|---------------------------|
| Category                    | Hoods / Housings          |
| Series of hoods/housings    | Han <sup>®</sup> B        |
| Type of hood/housing        | Bulkhead mounted housing  |
| Description of hood/housing | With thermo-plastic cover |
| Type                        | Low construction          |

## Version

|                            |                                                   |
|----------------------------|---------------------------------------------------|
| Size                       | 16 B                                              |
| Locking type               | Single locking lever                              |
| Han-Easy Lock <sup>®</sup> | Yes                                               |
| Field of application       | Standard hoods/housings for industrial connectors |

## Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Tightening torque                      | 1 Nm Fixing screws M4                          |
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Mating cycles                          | ≥500                                           |
| Degree of protection acc. to IEC 60529 | IP65<br>IP67                                   |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |



**Pushing Performance**  
Since 1945

## Material properties

|                                                            |                                                           |
|------------------------------------------------------------|-----------------------------------------------------------|
| Material (hood/housing)                                    | Aluminium die-cast                                        |
| Surface (hood/housing)                                     | Powder-coated                                             |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                                      |
| Material (seal)                                            | NBR                                                       |
| Material (locking)                                         | Polycarbonate (PC)<br>Stainless steel                     |
| Colour (locking)                                           | RAL 7037 (dust grey)                                      |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                                       |
| RoHS                                                       | compliant                                                 |
| ELV status                                                 | compliant                                                 |
| China RoHS                                                 | e                                                         |
| REACH Annex XVII substances                                | Not contained                                             |
| REACH ANNEX XIV substances                                 | Not contained                                             |
| REACH SVHC substances                                      | Yes                                                       |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| California Proposition 65 substances                       | Yes                                                       |
| California Proposition 65 substances                       | Nickel<br>Naphthalene                                     |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                      |
| Requirement set with Hazard Levels                         | R1 (HL 1-3)<br>R7 (HL 1-3)                                |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Packaging size                 | 1                                        |
| Net weight                     | 124.1 g                                  |
| Country of origin              | China                                    |
| European customs tariff number | 85389099                                 |
| GTIN                           | 5713140046245                            |
| eCl@ss                         | 27440202 Shell for industrial connectors |



Pushing Performance  
Since 1945

Commercial data

|             |          |
|-------------|----------|
| ETIM        | EC000437 |
| UNSPSC 24.0 | 39121466 |