

Han B Protect Cover Die Cast for Hoods



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 032 5420
Specification	Han B Protect Cover Die Cast for Hoods
HARTING eCatalogue	https://harting.com/09300325420

Identification

Category	Accessories
Series of hoods/housings	Han [®] B
Type of accessory	Protection cover
Description of the accessory	for hoods With fixing cord

Version

Size	32 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Metal
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	142.6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048232
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467