

## Han B Protect Cover Die Cast for Bases



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 30 032 5426                                                                |
| Specification      | Han B Protect Cover Die Cast for Bases                                        |
| HARTING eCatalogue | <a href="https://harting.com/09300325426">https://harting.com/09300325426</a> |

### Identification

|                              |                                                                                                |
|------------------------------|------------------------------------------------------------------------------------------------|
| Category                     | Accessories                                                                                    |
| Series of hoods/housings     | Han <sup>®</sup> B                                                                             |
| Type of accessory            | Protection cover                                                                               |
| Description of the accessory | for bulkhead mounted housings<br>for surface mounted housings<br>With fixing cord<br>for Pg 42 |

### Version

|              |                      |
|--------------|----------------------|
| Size         | 32 B                 |
| Locking type | Double locking lever |

### Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65            |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12   |

### Material properties

|                             |               |
|-----------------------------|---------------|
| Material (hood/housing)     | Metal         |
| RoHS                        | compliant     |
| ELV status                  | compliant     |
| China RoHS                  | e             |
| REACH Annex XVII substances | Not contained |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                              |
|--------------------------------------|------------------------------|
| REACH ANNEX XIV substances           | Not contained                |
| REACH SVHC substances                | Not contained                |
| California Proposition 65 substances | Yes                          |
| California Proposition 65 substances | Lead<br>Nickel               |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)         |
| Requirement set with Hazard Levels   | R22 (HL 1-3)<br>R23 (HL 1-3) |

## Specifications and approvals

|           |        |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

## Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 1                                      |
| Net weight                     | 102.6 g                                |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140163201                          |
| eCl@ss                         | 27440208 Cap for industrial connectors |
| ETIM                           | EC002314                               |
| UNSPSC 24.0                    | 39121467                               |