

Han E Male Contact CuNi 0.5 mm²/20 AWG



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6162
Specification	Han E Male Contact CuNi 0.5 mm ² /20 AWG
HARTING eCatalogue	https://harting.com/09330006162

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.5 mm ²
Conductor cross-section [AWG]	AWG 20
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	25
Net weight	1.45 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140049857
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522