



Pushing Performance
Since 1945

Han High Temp 6E-c Female



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 806 2704
Specification	Han High Temp 6E-c Female
HARTING eCatalogue	https://harting.com/09338062704

Identification

Category	Inserts
Series	Han E [®] High Temp

Version

Termination method	Crimp termination
Gender	Female
Size	6 B
Number of contacts	6
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm ²
Conductor cross-section [AWG]	AWG 20 ... AWG 14
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +200 °C With Han [®] High Temp components
Mating cycles	≥500



Pushing Performance
Since 1945

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390

Commercial data

Packaging size	1
Net weight	47.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140185838
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522