

Han PP PFT metal rectangular QL power



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 232 0311
Specification	Han PP PFT metal rectangular QL power
HARTING eCatalogue	https://harting.com/09352320311

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	Power
Element	Panel feed trough set
Specification	Rectangular panel cut out
Features	Intuitive locking mechanism

Version

Termination method	Han-Quick Lock® termination
Shielding	Unshielded
Number of contacts	5
Locking type	PushPull
Pack contents	incl. bulkhead mounted housing and male insert

Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm ²
Conductor cross-section [AWG]	AWG 24 ... AWG 12
Wire outer diameter	≤3.8 mm
Rated current	16 A
Rated voltage conductor-earth	400 V
Rated voltage conductor-conductor	690 V
Rated impulse voltage	6 kV
Pollution degree	2



Pushing Performance
Since 1945

Technical characteristics

Rated voltage acc. to UL	600 V
Limiting temperature	-40 ... +70 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67
Vibration resistance	5-150 Hz, 5 g, 0.35 mm, 2h/axis
Shock resistance	5 g / 30 ms, 3 shocks / axis and direction

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-3-118 EN 45545-2
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	31.74 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140054219
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408

Mating face

