

Han PP SCRJ Genderchanger



Image is for illustration purposes only. Please refer to product description.

Part number	09 35 241 0501
Specification	Han PP SCRJ Genderchanger
HARTING eCatalogue	https://harting.com/09352410501

Identification

Category	Connectors
Series	Han® PushPull (V14)
Identification	SCRJ
Element	Gender changer
Specification	AIDA compliant
Features	Intuitive locking mechanism

Version

Shielding	Unshielded
Number of contacts	2
Fixing	Wall mountable with 2 screws type M3
Locking type	PushPull

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 mated condition IP67 mated condition

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14)
	IEC 61754-24 Mating face
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	110 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140054424
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409