

## Han 6HP Direct cover device side



Image is for illustration purposes only. Please refer to product description.

Part number	09 39 006 5410
Specification	Han 6HP Direct cover device side
HARTING eCatalogue	<a href="https://harting.com/09390065410">https://harting.com/09390065410</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> HP Direct B
Type of accessory	Protection cover
Description of the accessory	for device side With fixing cord

### Version

Size	6 B
Locking type	Screw locking

### Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +120 °C
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

## Commercial data

Packaging size	1
Net weight	71.25 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140192294
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467