

Han 10HP Direct cover device side



Image is for illustration purposes only. Please refer to product description.

Part number	09 39 010 5410
Specification	Han 10HP Direct cover device side
HARTING eCatalogue	https://harting.com/09390105410

Identification

Category	Accessories
Series of hoods/housings	Han® HP Direct B
Type of accessory	Protection cover
Description of the accessory	for device side With fixing cord

Version

Size	10 B
Locking type	Screw locking

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +120 °C
Degree of protection acc. to IEC 60529	IP66

Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	RAL 7037 (dust grey)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	78.25 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140192300
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467