



Pushing Performance
Since 1945

Han 24HPR VarioShell-HBMA-SCL-SP2-3xM40



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 124 2333
Specification	Han 24HPR VarioShell-HBMA-SCL-SP2-3xM40
HARTING eCatalogue	https://harting.com/09401242333

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR VarioShell
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Angled

Version

Size	24 HPR VS
VarioShell level 1	3x M40
VarioShell level 2	3x SP2
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque	12 Nm Mounting frame
	10 Nm Mounting cover
	12 Nm PE screw
	3 Nm Fixing screws M6
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66
	IP67
	IP68
	IP69



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR

Specifications and approvals

Specifications	IEC 61984 IEC 61373 Category 1 Class B
Approvals	CE

Commercial data

Packaging size	1
Net weight	2,783.4 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140571419
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466