

Han3A RJ45 Cat5 plug 4p IDC, angled



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 115 1104
Specification	Han3A RJ45 Cat5 plug 4p IDC, angled
HARTING eCatalogue	https://harting.com/09451151104

Identification

Category	Connectors
Series	RJ45
Element	Cable connector
Specification	RJ45
Type of hood/housing	Hood
Description of hood/housing	Angled

Version

Termination method	IDC insulation displacement termination
Size	3 A
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Pack contents	Connector insert Hoods / Housings Cable gland Assembly instructions

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm ² Stranded 0.26 ... 0.32 mm ² Solid
Conductor cross-section [AWG]	AWG 24 ... AWG 22 Stranded AWG 23 ... AWG 22 Solid
Wire outer diameter	1.6 mm
Data rate	10 Mbit/s 100 Mbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-40 ... +70 °C
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	5 ... 9 mm

Material properties

Material (hood/housing)	Zinc die-cast
Colour (hood/housing)	Grey
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	EN 45545-2
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	8
Net weight	90 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140058750
eCl@ss	27440113 Rectangular connectors (set)
ETIM	EC002636



Pushing Performance
Since 1945

Commercial data

UNSPSC 24.0

39121408
