

PushPull V4 plug, RJ45, Cat.5



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 145 1106
Specification	PushPull V4 plug, RJ45, Cat.5
HARTING eCatalogue	https://harting.com/09451451106

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	RJ45
Element	Connector sets

Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Locking type	PushPull
Pack contents	incl. housing with RJ45 connector, shielding and cable gland

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm ² Stranded
	0.26 ... 0.32 mm ² Solid
Conductor cross-section [AWG]	AWG 24/7 ... AWG 22/7 Stranded
	AWG 23/1 ... AWG 22/1 Solid
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Tightening torque	1.3 ... 1.5 Nm
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	4.5 ... 10 mm
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction 5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	40.9 g
Country of origin	Romania
European customs tariff number	85366990



Pushing Performance
Since 1945

Commercial data

GTIN	5713140223721
eCl@ss	27440114 Rectangular connector (for field assembly)
ETIM	EC002636
UNSPSC 24.0	39121408