

USB 3.0 IP20 cable 0,5m, 2x type A 1:1




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 145 2930
Specification	USB 3.0 IP20 cable 0,5m, 2x type A 1:1
HARTING eCatalogue	https://harting.com/09451452930

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 3.0
Connector 1	IP20 USB 3.0 Type A
Connector 2	IP20 USB 3.0 Type A

Version

Cable length	0.5 m
Core structure	4x AWG 28/7 2x AWG 28/7 2x AWG 24/7
Shielding	Fully shielded, 360° shielding contact
Connection type	Type A connector - type A connector
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20
Cable diameter	5.8 mm



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	41.7 g
Country of origin	Malaysia
European customs tariff number	85444290
GTIN	5713140059214
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)