



Pushing Performance
Since 1945

USBC 3.2Type G.2x2 C-cable,2xIP20,1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 145 5901
Specification	USBC 3.2Type G.2x2 C-cable,2xIP20,1,0m
HARTING eCatalogue	https://harting.com/09451455901

Identification

Category	System cabling
Series	USB
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	USBC 3.2 Gen. 2x2
	Type C
	Male
	IP20
Connector 2	USBC 3.2 Gen. 2x2
	Type C
	Male
	IP20
Type of cable	Copper cable (round)
Features	supports USB Power Delivery (USB-PD)

Version

Cable length	1 m
Number of cores	24
Shielding	Shielded

Technical characteristics

Rated current	5 A
Rated voltage	20 V
Data rate	≤20 Gbit/s
Mating cycles	≥10,000



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	4.5 mm ± 0.2 mm
Vibration resistance	Category 1B acc. to IEC 61373
Shock resistance	Category 1B acc. to IEC 61373

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Net weight	44.5 g
Country of origin	China
European customs tariff number	85444290
GTIN	5713140571327
eCl@ss	27060390 Ready-made data cable (unspecified)
UNSPSC 24.0	26121600