



Pushing Performance
Since 1945

har-port RJ45 coupler Cat6A bk, 100 pcs.



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1561 XL
Specification	har-port RJ45 coupler Cat6A bk, 100 pcs.
HARTING eCatalogue	https://harting.com/09454521561XL

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	RJ45
Features	Suitable for all PoE versions

Version

Shielding	Fully shielded, 360° shielding contact
Connection type	Jack to jack
Fixing	Screwable in cover plates

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	10 Gbit/s
Ambient temperature	-25 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
-------------------------	----------------



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	Black
-----------------------	-------

Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	100
Net weight	24 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140222830
ETIM	EC002599
eCl@ss	27060304 Appliance cord (data cable)