

har-port USB 3.0 A-A; PFT



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1902
Specification	har-port USB 3.0 A-A; PFT
HARTING eCatalogue	https://harting.com/09454521902

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 3.0

Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	silver
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Specifications and approvals

Specifications	EN 45545-2
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	1.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140060470
eCl@ss	27060304 Appliance cord (data cable)
ETIM	EC002599
UNSPSC 24.0	43202222