



Pushing Performance  
Since 1945

# har-port USB charger 5V/1,5A silver



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1979
Specification	har-port USB charger 5V/1,5A silver
HARTING eCatalogue	<a href="https://harting.com/09454521979">https://harting.com/09454521979</a>

## Identification

Category	Connectors
Series	har-port
Element	Charging set
Specification	USB 3.0

## Version

Connection type	Type A jack
Fixing	Screwable in cover plates

## Technical characteristics

Output current	1.5 A
Input voltage	12 ... 24 V DC
Output voltage	5 V DC $\pm$ 0,25
Operating temperature	-40 ... +55 °C
Storage temperature	-40 ... +80 °C
Mating cycles	$\geq$ 1,500
Degree of protection acc. to IEC 60529	IP20

## Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	silver
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	0.017 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140223059
eCl@ss	27060304 Appliance cord (data cable)
ETIM	EC002599
UNSPSC 24.0	43202222