

Contact Block LED 230V Module



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 453 0401
Specification	Contact Block LED 230V Module
HARTING eCatalogue	https://harting.com/09454530401

Identification

Category	Operator interfaces
Element	Contact block
Specification	LED (230 V)

Version

Termination method	Screw termination
Number of contacts	2

Technical characteristics

Conductor cross-section	0.5 ... 2.5 mm ²
Rated current	≥0.001 A
Rated current	under laboratory conditions
Conditional short-circuit current	1,000 A
Stripping length	9 mm
Tightening torque	0.8 ... 1 Nm Screw terminal
Operating temperature	-25 ... +70 °C
Storage temperature	-50 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Lifetime	>40,000 h

Material properties

Colour (insert)	White
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	EN 60947-5-1
----------------	--------------

Commercial data

Packaging size	20
Country of origin	Germany
European customs tariff number	85318070
GTIN	5713140450332
eCl@ss	27371209 Bulb socket block for command and alarm devices
ETIM	EC000204
UNSPSC 24.0	39111803