

HPP V4 USB 2.0 type A to type B



Image is for illustration purposes only. Please refer to product description.

Part number 09 45 541 1910

Specification HPP V4 USB 2.0 type A to type B

HARTING eCatalogue <https://harting.com/09455411910>

Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	USB
Element	Adapter PCB
Specification	USB 2.0 type A to USB 2.0 type B USB 2.0 type B to USB 2.0 type A
Adapter for	Jack to jack

Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	4

Technical characteristics

Limiting temperature	-40 ... +70 °C
Mating cycles	≥750

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4)
Approvals	DNV GL


Commercial data

Packaging size	1
Net weight	7.68 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140061057
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522

Mounting instruction



Mounting instruction



housing 09455450042 and 09455450043

