

RJ45 coupler housing empty IP 65/67



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 805 0000
Specification	RJ45 coupler housing empty IP 65/67
HARTING eCatalogue	https://harting.com/09458050000

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Coupler

Version

Details	Please order insert separately.
Pack contents	Hoods / Housings Seal membrane for 6 - 9 mm / 4.5 - 7.5 mm cable

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP65 / IP67
Cable diameter	6 ... 9 mm 4.5 ... 7.5 mm

Material properties

Material (hood/housing)	Polyamide (PA)
Material flammability class acc. to UL 94	V-2
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Not contained
--------------------------------------	---------------

Commercial data

Packaging size	1
Net weight	40 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140224599
eCl@ss	27440190 Industry connector (unspecified)
ETIM	EC001264
UNSPSC 24.0	39121409