

UIC558-HBM/CM-18PIN



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 001 0302
Specification	UIC558-HBM/CM-18PIN
HARTING eCatalogue	https://harting.com/09580010302

Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC 558
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

Version

Number of contacts	18
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP69 / IPX9K acc. to ISO 20653 mated condition

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7035 (light grey)
Material (seal)	Silicone
Material (locking)	Stainless steel



Pushing Performance
Since 1945

Specifications and approvals

Specifications	UIC 50558
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	585 g
Country of origin	India
European customs tariff number	85389099
GTIN	5713140183933
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466