

UICIT_WMRF 8/8



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 001 0312
Specification	UICIT_WMRF 8/8
HARTING eCatalogue	https://harting.com/09580010312

Identification

Category	Hoods / Housings
Series	HARTING UIC
Identification	UIC IT
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	With metal cover

Version

Number of contacts	16
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Limiting temperature	-50 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 2004 (pure orange)
Material (seal)	Silicone
Material (locking)	Stainless steel



Pushing Performance
Since 1945

Specifications and approvals

Specifications	Inspired by UIC 50558
	Inspired by IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	0.05 kg
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466