

## DSUB SV MA SSDP ANG73-254 15P AU3



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 66 222 7802                                                                |
| Specification      | DSUB SV MA SSDP ANG73-254 15P AU3                                             |
| HARTING eCatalogue | <a href="https://harting.com/09662227802">https://harting.com/09662227802</a> |

### Identification

|                            |                  |
|----------------------------|------------------|
| Category                   | Connectors       |
| Series                     | D-Sub            |
| Identification             | Standard         |
| Element                    | Connector        |
| Description of the contact | Turned<br>Angled |

### Version

|                    |                                    |
|--------------------|------------------------------------|
| Termination method | Wave soldering termination         |
| Gender             | Male                               |
| Size               | D-Sub 2                            |
| Connection type    | Motherboard to daughtercard        |
| Number of contacts | 15                                 |
| Termination length | 3 mm                               |
| Locking type       | Fixing flange with thread 4-40 UNC |

### Technical characteristics

|                                    |                     |
|------------------------------------|---------------------|
| Distance between rows              | 2.54 mm             |
| Contact spacing (termination side) | 2.74 mm             |
| Rated current                      | 7.5 A               |
| Clearance distance                 | ≥1 mm               |
| Creepage distance                  | ≥1 mm               |
| Insulation resistance              | >10 <sup>10</sup> Ω |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                  |                           |
|----------------------------------|---------------------------|
| Contact resistance               | ≤10 mΩ                    |
| Tightening torque                | ≤0.6 Nm Female screw lock |
| Limiting temperature             | -55 ... +125 °C           |
| Insertion force                  | ≤50 N                     |
| Withdrawal force                 | ≥4.5 N<br>≤33 N           |
| Performance level                | 3                         |
| Mating cycles                    | ≥50                       |
| Test voltage U <sub>r.m.s.</sub> | 1 kV                      |
| Isolation group                  | IIIa (175 ≤ CTI < 400)    |
| PCB thickness                    | ≥1.6 mm                   |
| Installation height              | 7.3 mm                    |
| Hot plugging                     | No                        |

## Material properties

|                                           |                                                                       |
|-------------------------------------------|-----------------------------------------------------------------------|
| Material (insert)                         | Thermoplastic resin, glass-fibre filled (PBTP)<br>Shell: Plated steel |
| Colour (insert)                           | Black                                                                 |
| Material (contacts)                       | Copper alloy                                                          |
| Surface (contacts)                        | Noble metal over Ni                                                   |
| Material flammability class acc. to UL 94 | V-0                                                                   |
| RoHS                                      | compliant with exemption                                              |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight                |
| ELV status                                | compliant with exemption                                              |
| China RoHS                                | 50                                                                    |
| REACH Annex XVII substances               | Not contained                                                         |
| REACH ANNEX XIV substances                | Not contained                                                         |
| REACH SVHC substances                     | Yes                                                                   |
| REACH SVHC substances                     | Lead                                                                  |
| ECHA SCIP number                          | ecef7555-f643-4ceb-a337-fc54762297f1                                  |
| California Proposition 65 substances      | Yes                                                                   |
| California Proposition 65 substances      | Antimony trioxide<br>Lead<br>Nickel                                   |
| Fire protection on railway vehicles       | EN 45545-2 (2020-08)                                                  |



Pushing Performance  
Since 1945

Material properties

Requirement set with Hazard Levels R26

Specifications and approvals

|                |                       |
|----------------|-----------------------|
| Specifications | DIN 41652             |
| UL / CSA       | UL 1977 ECBT2.E102079 |

Commercial data

|                                |                        |
|--------------------------------|------------------------|
| Packaging size                 | 100                    |
| Net weight                     | 10.39 g                |
| Country of origin              | China                  |
| European customs tariff number | 85366990               |
| GTIN                           | 5713140082151          |
| ETIM                           | EC001136               |
| eCl@ss                         | 27440214 D-Sub coupler |