

D-Sub_CCH_S2_PP_PL_PLA



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 015 0210
Specification	D-Sub_CCH_S2_PP_PL_PLA
HARTING eCatalogue	https://harting.com/09670150210

Identification

Category	Hoods / Housings
Series	D-Sub
Type of hood/housing	Shell housing
Description of hood/housing	Cover lockable

Version

Size	D-Sub 2
Shielding	Shielded
Version	Top/side entry
Cable entry	3x
Cable fixing	Cable clamp
Locking type	PushPull
2 parts	Yes
Separable	Yes
Details	An external InduCom cable clamp or a crimp flange - ferrule combination can be used to gain more space in the housing.
Pack contents	2 blind plates internal cable clamp with screws

Technical characteristics

Tightening torque	0.35 Nm Cable clamp screw
Ambient temperature	-20 ... +90 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP30



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	3.3 ... 14 mm Please follow the assembly instructions!
Vibration resistance	Category 1B acc. to IEC 61373
Shock resistance	Category 1B acc. to IEC 61373

Material properties

Material (hood/housing)	Thermoplastic
Surface (hood/housing)	Metallised
Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	HB
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	10
Net weight	31.97 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140469938
eCl@ss	27440213 D-Sub hood
UNSPSC 24.0	39121416