

## D SUB IP 67\_15 POLE STRAIGHT



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 67 515 7615                                                                |
| Specification      | D SUB IP 67_15 POLE STRAIGHT                                                  |
| HARTING eCatalogue | <a href="https://harting.com/09675157615">https://harting.com/09675157615</a> |

### Identification

|                            |                    |
|----------------------------|--------------------|
| Category                   | Connectors         |
| Series                     | D-Sub              |
| Identification             | IP67               |
| Element                    | Connector          |
| Specification              | With rear frame    |
| Description of the contact | Turned<br>Straight |

### Version

|                    |                                    |
|--------------------|------------------------------------|
| Termination method | Solder cup termination             |
| Gender             | Male                               |
| Size               | D-Sub 2                            |
| Number of contacts | 15                                 |
| Locking type       | Fixing flange with thread 4-40 UNC |

### Technical characteristics

|                               |                         |
|-------------------------------|-------------------------|
| Conductor cross-section       | 0.5 mm <sup>2</sup>     |
| Conductor cross-section [AWG] | AWG 20                  |
| Rated current                 | 5 A                     |
| Clearance distance            | ≥1 mm                   |
| Creepage distance             | ≥1 mm                   |
| Insulation resistance         | > 5 x 10 <sup>9</sup> Ω |
| Contact resistance            | ≤10 mΩ                  |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                        |                                  |
|----------------------------------------|----------------------------------|
| Tightening torque                      | 0.4 ... 0.6 Nm Female screw lock |
| Limiting temperature                   | -25 ... +70 °C                   |
| Performance level                      | NM 30 (S4)<br>1                  |
| Mating cycles                          | ≥500                             |
| Degree of protection acc. to IEC 60529 | IP67                             |
| Test voltage $U_{r.m.s.}$              | 1.2 kV                           |
| Isolation group                        | IIIa ( $175 \leq CTI < 400$ )    |
| Hot plugging                           | No                               |

## Material properties

|                                           |                                                                     |
|-------------------------------------------|---------------------------------------------------------------------|
| Material (insert)                         | Thermoplastic resin, glass-fibre filled<br>Shell: brass, tin plated |
| Colour (insert)                           | Red                                                                 |
| Material (contacts)                       | Copper alloy                                                        |
| Surface (contacts)                        | Noble metal over Ni                                                 |
| Layer thickness                           | ≥0.76 µm                                                            |
| Layer thickness                           | ≥30 µinch                                                           |
| Material (seal)                           | Silicone                                                            |
| Colour (seal)                             | Red                                                                 |
| Material                                  | Thermoplastic resin, glass-fibre filled                             |
| Material flammability class acc. to UL 94 | V-0                                                                 |
| RoHS                                      | compliant with exemption                                            |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight              |
| ELV status                                | compliant with exemption                                            |
| China RoHS                                | 50                                                                  |
| REACH Annex XVII substances               | Not contained                                                       |
| REACH ANNEX XIV substances                | Not contained                                                       |
| REACH SVHC substances                     | Yes                                                                 |
| REACH SVHC substances                     | Lead                                                                |
| ECHA SCIP number                          | ecef7555-f643-4ceb-a337-fc54762297f1                                |
| California Proposition 65 substances      | Yes                                                                 |
| California Proposition 65 substances      | Lead<br>Nickel                                                      |



**Pushing Performance**  
Since 1945

## Specifications and approvals

|                |                       |
|----------------|-----------------------|
| Specifications | DIN 41652             |
| UL / CSA       | UL 1977 ECBT2.E102079 |

## Commercial data

|                                |                        |
|--------------------------------|------------------------|
| Packaging size                 | 50                     |
| Net weight                     | 13.72 g                |
| Country of origin              | Germany                |
| European customs tariff number | 85366990               |
| GTIN                           | 5713140094390          |
| ETIM                           | EC001136               |
| eCl@ss                         | 27440214 D-Sub coupler |