



Pushing Performance
Since 1945

Han Hand Crimp Tool



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0110
Specification	Han Hand Crimp Tool
HARTING eCatalogue	https://harting.com/09990000110

Identification

Category	Tools
Type of tool	Hand crimping tool
Description of the tool	Han D [®] : 0.14 ... 1.5 mm ² (in the range from 0.14 ... 0.37 mm ² only suitable for contacts 09 15 000 6104/6204 and 09 15 000 6124/6224) Han E [®] : 0.5 ... 4 mm ² Han-Yellock [®] : 0.5 ... 4 mm ² Han [®] C: 1.5 ... 4 mm ²
Type of drive	Can be processed manually

Version

Die set	HARTING W Crimp
Direction of movement	Parallel
Field of application	Recommended for production lines up to 10,000 crimping operations per year
Pack contents	Locator Han [®] C Locator Han E [®] Locator Han D [®] Please order Han-Yellock [®] separately.

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	10.000 (at least once a year)



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	680 g
Country of origin	Germany
European customs tariff number	82032000
GTIN	5713140105577
eCl@ss	21043811 Crimping pliers
ETIM	EC000168