



Pushing Performance
Since 1945

Battery Crimping Tool Set



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0990
Specification	Battery Crimping Tool Set
HARTING eCatalogue	https://harting.com/09990000990

Identification

Category	Tools
Type of tool	Battery crimping tool set
Description of the tool	Han D [®] : 0.14 ... 1.5 mm ² (in the range from 0.14 ... 0.37 mm ² only suitable for contacts 09 15 000 6104/6204 and 09 15 000 6124/6224) Han E [®] : 0.5 ... 4 mm ² Han [®] C: 1.5 ... 4 mm ²
Type of drive	Electrical Battery

Version

Die set	HARTING W Crimp
Direction of movement	Parallel
Field of application	Recommended for field use Recommended for production lines
Pack contents	Locator Han [®] C Locator Han E [®] Locator Han D [®] 2 power supplies (EU and US) Lithium-Ion battery RAML1225 10.8 V, 2.5 Ah

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Cycles cleaning / inspection	100
Cycles crimp check	1,000



Pushing Performance
Since 1945

Technical characteristics

Cycles service / maintenance 10.000 (at least once a year)

Commercial data

Packaging size	1
Net weight	3,036.7 g
Country of origin	Germany
European customs tariff number	84672920
GTIN	5713140277663
eCl@ss	21043811 Crimping pliers
ETIM	EC000168



Pushing Performance
Since 1945

