

## Han-Yellock M-c 1.5mm<sup>2</sup> (Ag)



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 11 05 000 6105                                                                |
| Specification      | Han-Yellock M-c 1.5mm <sup>2</sup> (Ag)                                       |
| HARTING eCatalogue | <a href="https://harting.com/11050006105">https://harting.com/11050006105</a> |

### Identification

|                 |               |
|-----------------|---------------|
| Category        | Contacts      |
| Series          | Han-Yellock®  |
| Type of contact | Crimp contact |

### Version

|                       |                   |
|-----------------------|-------------------|
| Termination method    | Crimp termination |
| Gender                | Male              |
| Manufacturing process | Turned contacts   |

### Technical characteristics

|                               |                     |
|-------------------------------|---------------------|
| Conductor cross-section       | 1.5 mm <sup>2</sup> |
| Conductor cross-section [AWG] | AWG 16              |
| Rated current                 | ≤20 A               |
| Contact resistance            | ≤2 mΩ               |
| Stripping length              | 6.5 mm              |

### Material properties

|                     |                                                        |
|---------------------|--------------------------------------------------------|
| Material (contacts) | Copper alloy                                           |
| Surface (contacts)  | Silver plated                                          |
| RoHS                | compliant with exemption                               |
| RoHS exemptions     | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status          | compliant with exemption                               |
| China RoHS          | 50                                                     |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | b51e5b97-eeb5-438b-8538-f1771d43c17d |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead                                 |
|                                      | Nickel                               |

## Specifications and approvals

|                |             |
|----------------|-------------|
| Specifications | IEC 60664-1 |
|                | IEC 61984   |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 100                                        |
| Net weight                     | 0.696 g                                    |
| Country of origin              | Germany                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140109360                              |
| ETIM                           | EC000796                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |