

Han-Yellock multiplier 2 and 3 bridged




Image is for illustration purposes only. Please refer to product description.

Part number	11 05 105 2823
Specification	Han-Yellock multiplier 2 and 3 bridged
HARTING eCatalogue	https://harting.com/11051052823

Identification

Category	Inserts
Series	Han-Yellock®
Element	Multiplier
Specification	2 Bridged contacts 3 Bridged contacts

Version

Gender	Female
Number of contacts	5

Technical characteristics

Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 3000 (flame red)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	1e38d35d-d1be-4585-8e03-95faccd739bf
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	2
Net weight	6.99 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140109735
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors