




Dummy number - not sold



Part number	11 12 300 0101
Specification	Dummy number - not sold

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Carrier hood
Description of hood/housing	Plain push button Without logo

Version

Size	Han-Yellock® 30
Locking type	Push button
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Un-/locking temperature	-10 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR
Material (locking)	Polyamide (PA) Stainless steel



Material properties

Colour (locking) Melon yellow

Material flammability class acc. to UL 94 V-0

Specifications and approvals

Specifications EN 60664-1
IEC 61984

Approvals DNV GL

CE Yes

Commercial data

Packaging size 1

Country of origin Germany

European customs tariff number 85366990

eCl@ss 27440202 Shell for industrial connectors