

## Han CGM-M M40x1,5 D.22-32mm



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 19 00 000 5098                                                                |
| Specification      | Han CGM-M M40x1,5 D.22-32mm                                                   |
| HARTING eCatalogue | <a href="https://harting.com/19000005098">https://harting.com/19000005098</a> |

### Identification

|                          |             |
|--------------------------|-------------|
| Category                 | Accessories |
| Series of hoods/housings | Han® CGM-M  |
| Type of accessory        | Cable gland |

### Technical characteristics

|                                        |                                                          |
|----------------------------------------|----------------------------------------------------------|
| Tightening torque                      | ≤15 Nm (depending on the cable and the seal insert used) |
| Wrench size                            | 50                                                       |
| Limiting temperature                   | -40 ... +100 °C                                          |
| Degree of protection acc. to IEC 60529 | IP68<br>IP69 / IPX9K acc. to ISO 20653                   |
| Size                                   | M40                                                      |
| Clamping range                         | 22 ... 32 mm                                             |
| Width across corners                   | 55 mm                                                    |

### Material properties

|                          |                                                        |
|--------------------------|--------------------------------------------------------|
| Material (cable glands)  | Brass                                                  |
| Material (seal)          | NBR                                                    |
| Material (clamping ring) | Polyamide (PA)                                         |
| Surface (accessories)    | Nickel plated                                          |
| RoHS                     | compliant with exemption                               |
| RoHS exemptions          | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status               | compliant with exemption                               |
| China RoHS               | 50                                                     |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| REACH Annex XVII substances          | Not contained                        |
| REACH ANNEX XIV substances           | Not contained                        |
| REACH SVHC substances                | Yes                                  |
| REACH SVHC substances                | Lead                                 |
| ECHA SCIP number                     | 6fb545c1-f438-46c2-b07a-8552e7e5a3d7 |
| California Proposition 65 substances | Yes                                  |
| California Proposition 65 substances | Lead                                 |
|                                      | Nickel                               |

## Specifications and approvals

|           |                                  |
|-----------|----------------------------------|
| UL / CSA  | UL 514B QCRV.E479780             |
|           | CSA-C22.2 No. 18.3 QCRV7.E479780 |
| Approvals | DNV GL                           |

## Commercial data

|                                |                                           |
|--------------------------------|-------------------------------------------|
| Packaging size                 | 1                                         |
| Net weight                     | 176 g                                     |
| Country of origin              | Germany                                   |
| European customs tariff number | 84849000                                  |
| GTIN                           | 5713140123847                             |
| eCl@ss                         | 27140801 Screwed cable gland (electrical) |
| ETIM                           | EC000441                                  |
| UNSPSC 24.0                    | 39121431                                  |